

Pushbutton, 15.2 mm, screw connector, momentary contact function, 1 NO, bezel white



Description

Pushbutton with mounting hole diameter 15.2 mm

Pushbutton with mounting hole diameter 15.2 mm, screw terminal



technical data

> general

| | |
|---|-------------------------------|
| Bezel color | white |
| Property of bezel / mushroom | opaque |
| Collar shape | round |
| Operating temperature, min. | -25 °C |
| Operating temperature, max. | 85 °C |
| Storage temperature, min. | -40 °C |
| Storage temperature, max. | 90 °C |
| illuminated | No |
| Packaging | Box |
| Packaging unit | 100 pcs. |
| Net weight | 5 g |
| Operating life | 25,000 cycles |
| B10 | 32,500 cycles |
| Degree of protection, front side, according to DIN EN 60529 | IP40 IP65 with sealing cap |
| Minimum order quantity (MOQ) | 100 pcs. |
| RoHS compliant | Yes |
| REACH compliant | Yes |
| Country of origin | HU |

direct links

> [RAFI eCatalog](#)

> mounting diameters

| | |
|--------------------------|---------|
| Outside dimension, width | 19 mm |
| Mounting hole | 15.2 mm |
| Mounting depth | 21.5 mm |
| Installation height | 8.2 mm |

> mechanical data

| | |
|------------------------|----------------------------|
| Terminal on the rear | Screw terminal |
| Fixing | Threaded ring |
| Actuation function | momentary contact function |
| Operating force, max. | 7.5 N |
| Operating travel, max. | 3 mm |
| Contact function | 1 NO |

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which may change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights.

date: Aug 23, 2025 page: 1/2

RAFI GmbH & Co. KG

Ravensburger Str. 128-134
88276 Berg / Ravensburg
Germany
www.rafi-group.com,
info.headquarters@rafi-group.com

| | |
|--------------------------|----------------|
| Contact system | Bridge contact |
| Contact material | Silver |
| > electrical data | |
| Rated voltage, max. | 250 V |
| Rated current, max. | 0.7 A |