




Part Number : [5035481822](#)
Product Description : SlimStack Board-to-Board Receptacle, 0.40mm Pitch, HRF (High Retention Force) Series, 0.70mm Mated Height, 2.60 Mated Width, 18 Circuits
Series Number : 503548
Status : Active
Product Category : Board-to-Board Connectors



Documents & Resources

Drawings
[5035481822_sd.pdf](#)

3D Models and Design Files
[5035481822.dxf](#)
[5035481822.pdf](#)
[5035481822_stp.zip](#)

Specifications
[5035489200-SPK-200.pdf](#)
[5035480003-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	503548
Description	SlimStack Board-to-Board Receptacle, 0.40mm Pitch, HRF (High Retention Force) Series, 0.70mm Mated Height, 2.60 Mated Width, 18 Circuits
Series Name	0.4, HRF 7S
Application	Board-to-Board
Component Type	PCB Receptacle
Product Name	SlimStack
UPC	191128129664

Electrical

Current - Maximum per Contact	0.3A
Voltage - Maximum	50V AC/DC

Physical

Circuits (Loaded)	18
Circuits (maximum)	18
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No
Lock to Mating Part	Yes
Mated Height	0.70mm
Mated Width	2.60mm

Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	14.180/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	0.40mm
Pitch - Termination Interface	0.40mm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.40mm Pitch SlimStack Board-to-Board Plugs	<u>503552</u>

This document was generated on Jan 25, 2025