




TE Internal #: 1487588-2
USB 4-Position Plug, Type A to Type B Cable Assembly, White
Cable, USB Type A Plug End A, USB Type B Plug End B, Double
Ended, 24 AWG / 28 AWG
[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > Multimedia Cable Assemblies > USB Cable Assemblies



Cable Assembly Type: **USB 4-Position Plug, Type A to Type B**
Cable Color: **White**
Cable Assembly (End A): **USB Type A Plug**
Cable Assembly (End B): **USB Type B Plug**
Cable Assembly Configuration: **Double Ended**

Features

Product Type Features

Cable Assembly Type	USB 4-Position Plug, Type A to Type B
Cable Assembly (End A)	USB Type A Plug
Cable Assembly (End B)	USB Type B Plug

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Equalized	No
Cable Color	White

Dimensions

Wire Size	24 AWG, 28 AWG
-----------	----------------

Operation/Application

Shielded	Yes
----------	-----

Other

Cable Assembly Configuration	Double Ended
------------------------------	--------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1487593-1
USB, A-BLUNT,28/24,WHT,2.0M



TE Part # 1487596-1
USB, A-B, 28/24, BLACK, 2.0M



TE Part # 292336-1
Std USB Type A, Flag, T/H




TE Part # 1487596-2
USB, A-B, 28/24, BLACK, 1.5M





TE Part # 1487596-3
USB, A-B, 28/24, BLACK, 1.8M



TE Part # 5353929-1
Std USB Type A, R/A, SMT, Offset, Panel




TE Part # 5787617-1
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,



TE Part # 1487588-1
USB, A-B, 28/24, WHITE, 2.0M

Customers Also Bought



TE Part #CEA270M04000051000
940 RECEPTACLE, SPEEDTEC-READY



TE Part #2273007-1
M8 x 1.0 straight socket Pigtail Shld



TE Part #2-1879021-7
SMW3 1R2 5%



TE Part #3-2176611-5
EP 2W (SS) 27R 5%




TE Part #350428-4
02P UMNL PIN HDR ASSY NATL AU



TE Part #4622236001
CGPT-R-12.7-0



TE Part #2-2176617-3
SMQW3W R82 5%



TE Part #GA100K6MBD425
MBD9-MBD



TE Part #1487598-2
USB, A-B, 25/20, BLACK, 5.0M



TE Part #800363-SF
FN281-6-06

Documents

Product Drawings

USB, A-B, 28/24, WHITE, 1.5M

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1487588-2_F.2d_dxf.zip

1487588-2

USB 4-Position Plug, Type A to Type B Cable Assembly, White Cable, USB Type A Plug End A, USB Type B Plug End B, Double Ended, 24 AWG / 28 AWG



English

Customer View Model

[ENG_CVM_CVM_1487588-2_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1487588-2_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.