



+ FIBER OPTICS

RUGGED FIBER CABLE ASSEMBLIES



✓ Active

TE CONNECTIVITY (TE)
FOSM LEAD LC/DPX ODVA - LC/DPX 100M

FullAXS | Fiber Optic , FSM

9-2061348-9
TE Internal Number: 9-2061348-9

Not Yet Reviewed for EU RoHS
Not Yet Reviewed for EU ELV

Cable Type Fiber Optic Cable (FOCAB) ODC
Fiber Diameter (µm) 9/125
Outside Cable Diameter 5.5 mm [.216 in]
Number of Fibers 2
Connector Color (End A) Blue

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

FIBER OPTIC LEAD 5.5 Mm LC/DPX WITH ODVA ADAPTER - LC/DPX SINGLE MODE 9/125
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Cable Type** Fiber Optic Cable (FOCAB) ODC
- Mode** Singlemode
- Connector Type (End A)** LC with ODVA Adapter
- Connector Type (End B)** LC
- Connector Style (End A)** Duplex
- Connector Style (End B)** Duplex
- Fiber Channel** No
- Product Type** Cable Assembly
- MPO Cable Assembly** No
- Cable Assembly Type** LC Duplex to LC Duplex

Configuration Features

- Number of Fibers** 2
- Cable Buffering** Tight Buffer
- Exit Angle to Exit Angle** 180° to 180°

Body Features

- Connector Color (End A)** Blue
- Connector Color (End B)** Blue
- Cable Color** Black
- Boot Type (Left)** Standard
- Boot Type (Right)** Bend Limiting
- Boot Color (Left)** Black
- Boot Color (Right)** Blue
- Protective Cap** Yes

Dimensions

- Fiber Diameter (µm)** 9/125
- Outside Cable Diameter** 5.5 mm [.216 in]

Other

- Cable Assembly Length (m)** 99 – 101

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
