


© 2026 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-26-271532	05MAR2026	SA	GH



SECTION A–A





TEPN		DESCRIPTION		SIZE	øD	ød	E	PKG TYPE	PKG QTY
CHLOROPRENE	NBR	CHLOROPRENE	NBR						
1SNG609019R0000	1SNG609027R0000	ECR-WG-NPT14-BL-A	ENBR-WG-NPT14-BL-A	NPT 1/4"	16.8±0.3	$11.7^{+0.2}_{-0.3}$	2.0±0.3	BAG	500
1SNG609020R0000	1SNG609028R0000	ECR-WG-NPT38-BL-A	ENBR-WG-NPT38-BL-A	NPT 3/8"	24.0±0.3	$16.4^{+0.2}_{-0.3}$	2.0±0.3	BAG	500
1SNG609021R0000	1SNG609029R0000	ECR-WG-NPT12-BL-A	ENBR-WG-NPT12-BL-A	NPT 1/2"	29.0±0.3	$20.4^{+0.2}_{-0.3}$	2.0±0.3	BAG	250
1SNG609022R0000	1SNG609030R0000	ECR-WG-NPT34-BL-A	ENBR-WG-NPT34-BL-A	NPT 3/4"	37.0±0.3	$26.0^{+0.2}_{-0.3}$	2.0±0.3	BAG	250
1SNG609023R0000	1SNG609031R0000	ECR-WG-NPT1-BL-A	ENBR-WG-NPT1-BL-A	NPT 1"	45.0±0.3	$32.6^{+0.2}_{-0.3}$	2.0±0.3	BAG	250
1SNG609024R0000	1SNG609032R0000	ECR-WG-NPT114-BL-A	ENBR-WG-NPT114-BL-A	NPT 1 1/4"	53.0±0.5	$41.4^{+0.3}_{-0.5}$	2.0±0.3	BAG	250
1SNG609025R0000	1SNG609033R0000	ECR-WG-NPT112-BL-A	ENBR-WG-NPT112-BL-A	NPT 1 1/2"	61.0±0.5	$47.2^{+0.3}_{-0.5}$	2.0±0.3	BAG	150
1SNG609026R0000	1SNG609034R0000	ECR-WG-NPT2-BL-A	ENBR-WG-NPT2-BL-A	NPT 2"	75.0±0.5	$59.0^{+0.3}_{-0.5}$	2.0±0.3	BAG	150

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN ISO 3302-1 M1-C

0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL: SEE TABLE

FINISH: –

DWN RAJAN N KASI 04MAR2022
CHK RAFEEQ MOHD 13FEB2022
APVD RAFEEQ MOHD 13FEB2022
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

CUSTOMER DRAWING

TE Connectivity

NAME: NPT-WASHER

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1SNP061325-0100	—

SCALE 1:1 SHEET 1 OF 1 REV A1

1470-19 (1/15)

Downloaded from Arrow.com.