


NOTE:
1.MATERIAL:
1.1 USB-C PLUG CONN (P/N:10133475)
1.2 PCB (CUSTOMIZED)
2.LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008
3.PRODUCT IS HALOGEN FREE PRODUCTS.
4.DIMENSIONING SHALL BE INTERPRETED PER ANSI Y14.5-2009;
5.THIS DESIGN COMPLY WITH UNIVERSAL SERIAL BUS TYPE-C SPECIFICATION


PART MUNBER CODE:10144277 - X 0 0 0 X LF

- CONN OPTION
0. 10133475-10000LF
1. 10133475-10001LF
- PCB AND ELECTRON COMPONENT OPTION
2: WITH PCB STYLE 2 (REF SHEET 2)
3: WITH PCB STYLE 3 (REF SHEET 3)
4: WITH PCB STYLE 4 (REF SHEET 4)
5: WITH PCB STYLE 5 + FEMALE HEADER 10 POS CONN (REF SHEET 5)
6: WITH PCB STYLE 6 + HEADER 10POS CONN+ RESISTORS (REF SHEET 6)
7: WITH PCB STYLE 7 (REF SHEET 7)
8: WITH PCB STYLE 8 (REF SHEET 8)




spec ref -				dr	Li-Qing Lei	2017/06/13			size	A3	scale	1.000
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Li-Qing Lei	2021/08/05			ecn no	ELX-N-41918-1		
ISO 406 ISO 1101				chr	-	-			rel level	Released		
				appr	Tim Yao	2021/08/30	product family					
 surface ISO 1302	linear	0.X	±0.35	Amphenol FCi	title	USB Type-C CABLE PLUG KITS			dwg no	10144277		rev F
		0.XX	±0.25									
		0.XXX	±0.15									
	angular	0°	±2°			cat. no.	Product - Customer Drw			sheet 1 of 8		



PART MUNBER
10144277-20000LF






PCB STYLE 2



- 1. MATERIAL: FR-4, DOUBLE LAYER;
- 2. CU THICKNESS: 1 OZ
- 3. SURFACE TREATMENT: TIN COATING


spec ref -				dr		Li-Qing Lei	2017/06/13			size	A3	scale	5.000						
tolerance std				eng		Li-Qing Lei	2021/08/05			ecn no				ELX-N-41918-1					
ISO 406 ISO 1101				chr		-	-			rel level				Released					
TOLERANCES UNLESS OTHERWISE SPECIFIED				appr		Tim Yao	2021/08/30	product family											
surface			linear	0.X	±0.35					title USB Type-C CABLE PLUG KITS				dwg no		10144277		rev	F
ISO 1302			0.XX	±0.25															
			0.XXX	±0.15															
		angular	0°	±2°	cat. no.				Product - Customer Drw				sheet 2 of 8						

PART MUNBER
10144277-30000LF




spec ref -				dr	Li-Qing Lei	2017/06/13	projection	mm	size	A3	scale	1.000
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Li-Qing Lei	2021/08/05			ecn no ELX-N-41918-1			
				chr	-	-			rel level Released			
				appr		Tim Yao			2021/08/30	product family		
surface ISO 1302	linear	0.X	±0.35	Amphenol FCi	title USB Type-C CABLE PLUG KITS				dwg no	10144277		rev F
		0.XX	±0.25									
		0.XXX	±0.15									
	angular	0°	±2°	cat. no.	Product - Customer Drw				sheet 3 of 8			


PART MUNBER
10144277-40000LF






PCB STYLE 4





1. MATERIAL: FR-4, DOUBLE LAYER;
2. CU THICKNESS: 1 OZ
3. SURFACE TREATMENT: IMMERSION GOLD

spec ref -				dr Li-Qing Lei		2017/06/13				size A3		scale 4.000	
tolerance std				eng Li-Qing Lei		2021/08/05				ecn no ELX-N-41918-1			
ISO 406				chr -		-				rel level Released			
ISO 1101				appr Tim Yao		2021/08/30				product family			
surface ISO 1302		linear	0.X	±0.35		title USB Type-C				dwg no 10144277		rev F	
			0.XX	±0.25									
			0.XXX	±0.15									
		angular	0°	±2°		cat. no.		Product - Customer Drw					

PART MUNBER
10144277-50000LF



1. MATERIAL: FR-4, DOUBLE LAYER;
2. CU THICKNESS: 1 OZ
3. SURFACE TREATMENT: IMMERSION GOLD

spec ref -				dr	Li-Qing Lei	2017/06/13			size	A3	scale	1.000
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Li-Qing Lei	2021/08/05			ecn no ELX-N-41918-1			
				chr	-	-			rel level Released			
				appr		Tim Yao			2021/08/30	product family		
surface ISO 1302	linear	0.X	±0.35		title USB Type-C CABLE PLUG KITS				dwg no	10144277		rev F
		0.XX	±0.25									
		0.XXX	±0.15									
	angular	0°	±2°	cat. no.	Product - Customer Drw				sheet 5 of 8			


PART MUNBER
10144277-60000LF

A


B

C


D






PCB STYLE 6






1. MATERIAL: FR-4, DOUBLE LAYER;
2. CU THICKNESS: 1 OZ
3. SURFACE TREATMENT: IMMERSION GOLD

spec ref -				dr Li-Qing Lei		2017/06/13				size A3		scale 1.000	
tolerance std				eng Li-Qing Lei		2021/08/05				ecn no ELX-N-41918-1			
ISO 406				chr -		-				rel level Released			
ISO 1101				appr Tim Yao		2021/08/30				product family			
surface ISO 1302		linear	0.X	±0.35		title USB Type-C				dwg no 10144277		rev F	
			0.XX	±0.25									
			0.XXX	±0.15									
		ISO 1302	angular	0°		±2°	cat. no.		Product - Customer Drw				sheet 6 of 8

PART MUNBER	COLOR OF THE DOT
10144277-70000LF	BLACK
10144277-70001LF	WHITE



PCB STYLE 3



THERE'S A COLORED DOT HERE,
1. IF THE COLOR IS BLACK, THE P/N OF THE FINISHED GOODS IS 10144277-70000LF
2. IF THE COLOR IS WHITE, THE P/N OF THE FINISHED GOODS IS 10144277-70001LF

PCBA IS CUSTOMIZED

spec ref	-	dr	Li-Qing Lei	2017/06/13	projection	mm	size	A3	scale	1.000
tolerance std	ISO 406 ISO 1101	eng	Li-Qing Lei	2021/08/05	chr	-	ecn no	ELX-N-41918-1	rel level	Released
surface	linear	appr	Tim Yao	2021/08/30	product family	USB Type-C CABLE PLUG KITS	dwg no	10144277	rev	F
ISO 1302	angular	0°	±2°	cat. no.	Product - Customer Drw	sheet 7 of 8				

