













GENERAL CHARACTERISTICS

Operating Force	Max. 140gf
Release Force	Min. 20gf
Contact Resistance	Max. 50mΩ
Insulation Resistance	Min. 100MΩ 500VDC
Dielectric Voltage	AC500V 60 Sec.
Mechanical Life	1,000,000 Cycles
Rating (UL/ENEC Certified)	3(0.5)A 125/250VAC 25,000 Cycles
Rating (UL Certified)	3A, 30VDC 25,000 Cycles
Operating Temperature	-25 to 125°C





Circuit Diagram



The date code could be printed on each lateral side randomly

NO.	PARTS	MATERIALS
01	COVER	PBT 94V0
02	BASE	PBT 94V0
03	ACTUATOR	PBT 94V0
04	CONTACT	Ag ALLOY
05	MOVING BLADE	COPPER BERYLLIUM
06	TERMINAL(COM)	SILVER PLATE BRASS
07	TERMINAL(NO)	SILVER PLATE BRASS
08	TERMINAL(NC)	SILVER PLATE BRASS

Further details please refer to technical specification TS-DG-00001.
In case there are any deviations the drawing details have priority.

记号 MARK.	变更内容 DEFINITION	修改 REVISE	核准 APPROVE	日期 DATE	批准: APPROVE			
3					制图: DRAW	H,QIN	2020.12.11	TOLERANCE UNLESS SPECIFLED
2					设计: DESIGN	H,QIN	2020.12.11	WITHIN 1.5mm: ±0.1mm OVER 1.5mm: ±0.2mm
1	Rating	H,QIN	J.WANG	2024.05.15	审核: CHECKED	J.WANG	2020.12.16	材质: MATERIAL
					批准: APPROVE	J.WANG	2020.12.16	单位: UNIT mm

采埃孚电子(珠海)有限公司
ZF Electronics (Zhuhai) Company Limited

系列 SERIES	DG 3A微动开关/SUBMINIATURE SWITCH				
料号: TITLE	DGE3-E7AA	图号: DWG NO.	DGE3-E7AA		
比例: SCALE	1:1	角法: PROJ.	张数: SHEET	第1页,共1页	工程图 ENG. DWG / 版本: REV. A0

Downloaded from Arrow.com.