

# Hospital-Grade Power Cord, NEMA 5-15P to C13 - Green Dot, 10A, 125V, 18 AWG, 8 ft. (2.43 m) Coiled Cord, Black

MODEL NUMBER: P006-C08-HG10



Coiled medical power cord connects your PC or other hospital equipment with a C14 inlet to a grounded hospital-grade AC outlet.

## Features

**Hospital-Grade Power Cable is a Safe Solution for Medical Facilities** This hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment with a three-pin C14 inlet. It features a C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient-care vicinities.

**Coiled Power Cord Allows You Freedom of Movement** The NEMA 5-15P-HG hospital-grade plug is connected to a coiled power cord that fully extends to 8-ft. (2.43 m). The cord is designed to resist tangles and knots, and it takes up less space when not stretched to its full length. Best of all, the coiled cable gives you more freedom in placing the power strip where it's most needed at any given time.

**Designed and Tested to Strict Hospital-Grade Standards** The hospital-grade power cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

## Specifications

OVERVIEW	
UPC Code	037332193322
Product Type	Hospital Grade
Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10

## Highlights

- Recommended for connecting devices to power outlets outside patient-care vicinities
- Coiled cord extends to 8-ft. (2.43 m) to allow flexibility in placing devices away from AC outlet
- Medical power cord replaces or upgrades power cord provided by manufacturer
- NEMA 5-15P-HG plug connects to AC power; C13 plug connects to device's C14 inlet

## Applications

- Connect devices like PCs, mobile carts, monitors and printers to a power outlet up to 8-ft. (2.43 m) away in a hospital environment outside patient-care vicinities
- Extend an existing power connection up to 8-ft. (2.43 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

## Package Includes

- P006-C08-HG10 Hospital-Grade Power Cord, NEMA 5-15P to C13, 8-ft. (2.43 m) Coiled, Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Voltage Compatibility (VAC)	125
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P-HG
Side B - Connector 1	IEC-320-C13
Connector Style	Straight
<b>PHYSICAL</b>	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Power Cord Color	Black
Cable Length (ft.)	8
Cable Length (m)	2.44
Coiled Length (ft.)	8
Uncoiled Length (ft.)	8.67
Shipping Dimensions (hwd / in.)	7.00 x 9.90 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 25.15 x 1.27
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
Unit Dimensions (hwd / in.)	7.000 x 9.900 x 0.500
Unit Weight (lbs.)	0.6
Unit Weight (kg)	0.27
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH



Powering Business Worldwide

TRIPP LITE  
SERIES

FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
Locking Power Cord	No
Locking	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.