


[Company information](#)
[Product information](#)
[support](#)
[IR information](#)
[Sales network](#)
[Recruitment information](#)
[Home](#) > [Products](#) > [Product Details](#)


Push button M series **MB-2511V**



* Photo is a sample image.
Colors and shapes may differ from the real ones.
* Please confirm the actual color and shape with product samples.

 [Display product drawing](#)
 [2D DXF](#)
 [PDF](#)
[Purchase](#)

Product introduction

Light touch push button (M series), PC-V terminal type (gold-plated contact): Single pole, double throw · Every market needs: 126000 models · Case of UL 94V-0 · Improved insulation · High contact reliability of contact parts · Shut out of flux etc. · Operating temperature range: -30 to 85 °C · Applications: OA equipment, radio equipment, professional video Cameras, exchanges, electrical measuring instruments, control panels, etc., EU-RoHS compliant Model name: MB-2511V

Product Summary

Model name	MB-2511V
category	Push button
series	M
Subcategory	Non-illuminated switch
Current capacity for detailed display 1	0.4VA MAX. 28V MAX.
Operating temperature range (°C)	-30 / + 85
Number of poles	Single pole
Function 1	ON- (ON)
Function 2	Momentary
Operation section shape	Sold separately: Circle 8, Circle 10
Terminal shape	Printed circuit board vertical
Dimensions guide 1 (unit: mm length * width * back)	13 × 26.48 × 7.9
External dimensions 2 (conditions)	Excluding the operation unit, the height is the top surface of the board
Acquisition standard	CSA, UL
Acquisition standard model name	MB-2511VCSA, MB-2511VUL
Environmental performance	RoHS

Specification change

No.	category	Overview	date of issue	PDF
352	Specification change	Compliant with the banned substance standards of 10 substances regulated by EU-RoHS Directive Compliant by July 22, 2019	April 26, 2019	
265	Specification change	Transfer of production from Chinese factory to Philippine factory	October 30, 2015	
238	Specification change	Change of plunger tip shape	July 31, 2014	

Selected parts

Please use in combination.

-  Button round AT-442-B (button round / blue)
-  Button round AT-442-K (button round / black)
-  Button round AT-442-M (button round / green)
-  Button round AT-442-R (button round / red)
-  Button round AT-442-W (button round / white)
-  Button round AT-442-Y (button round / yellow)
-  Button round AT-443-B (button round / blue)
-  Button round AT-443-K (button round / black)
-  Button round AT-443-M (button round / green)
-  Button circle AT-443-R (button circle / red)

12 results

Next 
 Previous

To series TOP 