



PLUGGABLE I/O CABLE ASSEMBLIES



✓ Active

[Download](#) **PRODUCT DRAWING**
English

TE CONNECTIVITY (TE) CA 75MM 14 POS. MOW-PB M-M VALUE LINE

2205117-1
TE Internal Number: 2205117-1

[Always EU RoHS/ELV Compliant](#)

Cable Assembly Type **MOW to PB**

Equalized **No**

Wire Size (AWG) **28**

Cable Assembly Length **.075 m [.246 ft]**

Color **Gray**

Product Drawings

[CABLE ASSY MICRO-MATCH MOW-PB VALUE-LINE](#)
PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Cable Assembly Type	MOW to PB
	Product Type	Cable Assembly
	Cable Assembly Category	Industry Standard
	Product Designation	Patch Cord
Configuration Features	Number of Power Positions	14
	Keyed	No
	Configuration	Double-Ended
Body Features	Equalized	No
	Color	Gray
Dimensions	Wire Size (AWG)	28
	Cable Assembly Length	.075 m [.246 ft]

Industry Standards	Flammability Rating	UL 2651
	IEEE 1394	No
Other	CLOUDSPLITTER	No
Product Compliance	Statement of Compliance	
	PDF	
	VIEW ALL PRODUCT COMPLIANCE	