Representative Image

Catalog No. TC104

Description: MINI MTG BASE .4X.3IN NAT NYL SCREW

UPC No 5414363057888

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Miniature Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 10.3mm (0.406 Inches), Width of 7.92mm (0.312 Inches), Height of 2.4mm (0.094 Inches), #5 Screw Mounting Method

Descriptors

Category	Cable tie mounts
Special Features	These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap

Dimensions

Mount Size	#5

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	10.3 mm
Length	0.41 inch
Width	7.92 mm
Width	0.312 inch

Downloaded from Arrow.com.

ETIM	EC000449 Mounting base and -element for cable ties
Height	2.4 mm
Height	0.09 inch
Type of fastening	Other
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	ZODZ	N/A	N/A

Downloaded from Arrow.com.