

SERIES KMA 301

Ø 3 mm LED

TYPE (1 LED)	EMITTED COLOUR	LUMINOUS INTENSITY		FULL VIEWING ANGLE	FORWARD VOLTAGE (IF = 20 mA)		OPERATING TEMPERATURE	FORWARD CURRENT	
		PEAK	TYP.		IF	TYP.			MAX
KMA 301 - R	RED	700	5	10	120	2,0	2,5	- 55 to + 100	25
KMA 301 - Y	YELLOW	590	12,5	10	120	2,1	2,5		30
KMA 301 - G	GREEN	565	12,5	10	120	2,2	2,5		25
KMA 301 - S	SUPER RED	625	20	10	120	2,0	2,5		30
KMA 301 - B	RED/GREEN	625/565	12,5	20	120	2,0	2,5		25
KMA 301 - I	I PER RED	660	100	20	120	1,85	2,5		30
LOW CURRENT									
KMA 301 - RL	RED	625	2	2	120	1,8	2,5	- 55	7,5
KMA 301 - YL	YELLOW	590	2	2	120	1,9	2,7	to	7,5
KMA 301 - GL	GREEN	565	2	2	120	1,9	2,5		7,5
KMA 301 - IL	I PER RED	660	20	2	120	1,85	2,5	+ 100	7,5
QUALITY TESTED 100%	DIFFUSED	nm	mcd	mA	DEGREE°	V	V	°C	mA

