Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

APC IT Power Distribution Module 3 Pole 4 Wire 50A CS50 680cm



PDM3450CS50-680

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Shins within 3 Weeks

Main

Main Input Voltage	208 V 3 phases
Main Output Voltage	208 V 3 phases
Output connector type	CS50 1
Provided equipment	Installation guide

Physical

Colour	Black
Height	12.7 cm
Width	44.5 cm
Depth	40.6 cm
Net weight	5.18 kg

Input

Network frequency	60 Hz
Permissible voltage	200240 V
Max line current	50 A

Output

Max current draw	50 A
Number of power socket outlets	1 CS50

Conformance

Product certifications UL listed

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.7 cm

Jul 8, 2025

Package 1 Width	40.6 cm
Package 1 Length	44.5 cm
Package 1 Weight	5 73 kg

Contractual warranty

Warranty 1 year repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Ø	Environmental	footprint

Environmental Disclosure Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Under investigation

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	Yes

Jul 8, 2025