172199-1 ✔ ACTIVE

TE Internal #: 172199-1

TE Internal Description: ECONOSEAL-J CONN CAP 2P NATURA ECONOSEAL, CONNECTOR HOUSING

View on TE.com >







All ECONOSEAL, CONNECTOR HOUSING (61)

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Downloaded from Arrow.com.

Compatible Parts




TE Part # 172190-3
ECONOSEAL-J O-RING 2, 3P



TE Part # 172198-2
ECONOSEAL-J CONN PLUG 2P BLACK



TE Part # 2822397-3
ECONOSEAL 2,3P O RING




TE Part # 172200-1
ECONOSEAL-J CONN RUBBER 2P

Customers Also Bought



TE Part #NB10132001
ATUM-24/6-0-STK



TE Part #172200-1
ECONOSEAL-J CONN RUBBER 2P



TE Part #175289-3
DYNAMIC D-3 TAB CONT. L AU 0.76 L /P



TE Part #316836-1
040-3 REC CONT. S



TE Part #1-480699-0
02P UMNL CAP HSG NATL



TE Part #1-480701-0
03P UMNL CAP HSG NATL



TE Part #926893-1
UNIV.M-N-L.SOCKET CONTACT



TE Part #170279-1
2 DIA PIN LANCE-LESS



TE Part #170280-1
2 DIA PIN RECP LANCE-LESS ASSY



TE Part #2822397-3
ECONOSEAL 2,3P O RING

Documents

Product Drawings

ECONOSEAL-J CONN CAP 2P NATURA

Japanese

CAD Files

3D PDF

3D

Downloaded from Arrow.com.

Customer View Model

ENG_CVM_CVM_172199-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_172199-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_172199-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

Econoseal Connector Series

English

Product Specifications

Product Specification

Japanese

Instruction Sheets

AMP ECONOSEAL* SERIES "J" CONNECTOR

English

AMP ECONOSEAL* SERIES "J" CONNECTOR

English

AMP ECONOSEAL* SERIES "J" CONNECTOR

Japanese

AMP ECONOSEAL* SERIES "J" CONNECTOR

Japanese

Downloaded from Arrow.com.