



Part Number : [936010478](#)

Product Description : Heavy-Duty Turned Crimp Contact for 5A D-Sub Inserts and Modules, Female, Gold (Au) Plated Copper Alloy, 0.35-0.50mm² (22-20 AWG), 100 per Bag

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Contacts

Engineering Part Number : 7700.3438.1



Documents and Resources

Drawings

[936010478_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025) SCIP:00f6ad53-8357-44ef-a11f-17fcbf1b565a
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Contacts
Series	93601
Description	Heavy-Duty Turned Crimp Contact for 5A D-Sub Inserts and Modules, Female, Gold (Au) Plated Copper Alloy, 0.35-0.50mm ² (22-20 AWG), 100 per Bag
Contact Type	Turned Crimp
Product Name	Heavy-Duty Connectors
UPC	887191892863

Electrical

Current - Maximum per Contact	5.0A
-------------------------------	------

Physical

Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Gold
Net Weight	0.210/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	5.00mm
Wire Size (AWG)	20, 22
Wire Size mm ²	0.35-0.50

Mates With / Use With

Mates with Part(s)

Description	Part Number
GWconnect Heavy-Duty Connectors and Accessories	<u>93601</u>

Use with Part(s)

Description	Part Number
Use With	D-Sub Connectors

This document was generated on Dec 16, 2025