

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-25-232225	16JAN2025	SC	D.Z



SECTION A-A





NOTE,

1. APPLICABLE WIRE : UL1015 TYPE, AWG #16~#12

108-5979	4-1871867-X 4-1746978-X	BLACK	1-2232564-1
108-78232	1747995-*		
PRODUCT SPEC	MATING P/N	COLOR	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±- ±0.3
2 PLC ±- ±5°
3 PLC ±-
4 PLC ±-
ANGLES ±-°

MATERIAL: PA66 UL94 V-0

FINISH: - -

DWN ANNIE QIAN 27-SPE-16
CHK ANNIE QIAN 27-SPE-16
APVD DANIEL ZHANG 27-SPE-16
PRODUCT SPEC: SEE TABLE
APPLICATION SPEC: 114-5356
WEIGHT: -

TE Connectivity

NAME: GRACE HI-CURRENT(GHC) 6.2mm 3POS TPA HOUSING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2232564	

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV A1

1470-19 (3/13)

Downloaded from Arrow.com.