

Han-Eco Mod.16 flange gasket-HBM



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 000 9803
Specification	Han-Eco Mod.16 flange gasket-HBM
HARTING eCatalogue	https://harting.com/19410009803

Identification

Category	Accessories
Series of hoods/housings	Han-Eco® Modular
Type of accessory	Flange gasket

Version

Size	16 B
------	------

Material properties

Material (seal)	NBR
Colour (seal)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Commercial data

Packaging size	10
----------------	----



Pushing Performance
Since 1945

Commercial data

Net weight	9.5 g
Country of origin	Germany
European customs tariff number	40169300
GTIN	5713140130609
eCl@ss	27440291 Connector component (parts)
ETIM	EC002943
UNSPSC 24.0	39121400