



Part Number : [192150115](#)

Series Number : 19215

Product Category : Splices

Product Description : VersaKrimp Butt Splice for 14-16 AWG Wire, Tape and Reel

Status : Active

Engineering Number : BS-331T

---

## Documents & Resources

### Drawings

[Drawing 192150115\\_sd.pdf](#)

### Specifications


[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-015-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### [EU RoHS Certificate of Compliance](#)

---

## Part Details

### General

Status	Active
Category	Splices
Series	19215
Description	VersaKrimp Butt Splice for 14-16 AWG Wire, Tape and Reel
Product Family	Splices
Product Name	Butt,VersaKrimp
UPC	800753055407

### Agency

UL	E32244
----	--------

### Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.094/g
Packaging Type	Adhesive Tape on Reel
Wire Size (AWG)	14, 16

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

### Application Tooling

### Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>190270055</u>
Mini-Mac Applicator	<u>638858100</u>

---

This document was generated on Jul 29, 2024