


REV. 0
DCO 141722

COIL: @ 25°C

RESISTANCE 3300 OHMS ±10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 14.0 VDC

MUST RELEASE 1.4 VDC

ENVIRONMENT:


VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX
RELEASE TIME 7.5 MS MAX
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 2/2/00 CK. 2/2/00

COMMUNICATIONS INSTRUMENTS, INC.

CUST. C.I.I. STD.
CUST. NO. _____ REV. _____

"MSD" RELAY

MSPD-26

F-715 REV. 2

Downloaded from Arrow.com.