Specifications



Photo is representative





Eaton DR124-331-R

Eaton DR124 inductor, 330uH, 0.83A Irms, 0.92A ISAT, 990 mOhm resistance, SMT mounting, Ferrite, 2-pins, 750 qty.

General specifications	
PRODUCT NAME	Eaton DR124 inductor
CATALOG NUMBER	DR124-331-R
UPC	051712825573
PRODUCT LENGTH/DEPTH	12.5 mm
PRODUCT HEIGHT	4.5 mm
PRODUCT WIDTH	12.5 mm
PRODUCT WEIGHT	2.224 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.83 A
ISAT	0.92 A
PACKAGE QUANTITY	750
MATERIAL	Ferrite
AUTOMOTIVE GRADE	No
FREQUENCY RATING	Up to 1 MHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	990 mΩ
TERMINALS	12.5x12.5x4.5mm
SERIES	DR124

Resources

SPECIFICATIONS AND DATASHEETS	Eaton DR124 shielded drum core power inductors data sheet Eaton Specification Sheet - DR124-331-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.