

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1731120201

Status:

Active

Overview:

FCT D-Sub Connectors

Description:

FCT Machined Contact, Male, Crimp, 0.80µm Gold Plating, 20-24 AWG

Documents:

Packaging Specification 1731120004-PK-000 (PDF)

Brochure (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

D-Sub Products

Series

173112

Contact Type

Machined Crimp

Overview

FCT D-Sub Connectors

Product Category

Contacts

Product Name

FCT Products

Taxonomy

D-Sub Contacts

Type

Standard Density

UPC

889056489560

Physical

Durability (mating cycles max)

500

Gender

Male

Material - Contact

Brass

Net Weight

0.200/g

Orientation

Straight

Packaging Type

Bag

Plating - Contact

Gold over Nickel

Plating min - Mating

0.800µm

Plating min - Termination

0.800µm

Temperature Range - Operating

-55° to +130°C

Termination Style

Crimp

Wire Size AWG

20, 22, 24

Electrical

Current - Maximum per Contact

7.5A

Material Info

Engineering Number

FK20P-08V-5783

Reference - Drawing Numbers

Packaging Specification

1731120004-PK-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

173112 Series

Use With

FCT Standard-Density Connectors

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION