

Keystone Patch panel, loaded



Image is for illustration purposes only. Please refer to product description.

Part number	20 82 405 0001
Specification	Keystone Patch panel, loaded
HARTING eCatalogue	https://b2b.harting.com/20824050001

Identification

Category	Connectors
Series	preLink®
Element	Patch panel

Version

Size	Keystone version
Fixing	In 19" racks acc. to IEC/DIN EN 60 297-3-100 (DIN 41 494-1)
Pack contents	24 preLink® RJ45 keystone jack 24 terminal modules for AWG 22 / 23 24 cable ties

Technical characteristics

Limiting temperature	-40 ... +85 °C
Degree of protection acc. to IEC 60529	IP20
Transmission characteristics	Cat. 6 Class E up to 250 MHz
Data rate	10 Gbit/s
Vibration resistance	5.72 m/s ² acc. to IEC 61373 Category 1 Class B
Shock resistance	5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Material (insert)	Steel sheet
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	1,607.2 g
Country of origin	Czechia
European customs tariff number	85389099
eCl@ss	27440292 Connector component (accessories)