



Datasheet for part number MDM-15PH006B-A174-F222

Our Catalog Part Number: MDM-15PH006B-A174-F222
Our Global Manufacturing Part Number: 096512-0976
Brand: Cannon Product Category: Micro Product Line: Micros Series: MICRO

Product Datasheet	
Series	Micro "D" Metal Shell
Arrangement	15 Contact
Gender	Pin
Contact Material	Gold plated copper alloy
Contact Type	Crimp
Contact Resistance	8 milliohms max.
Termination Type	36" Min, M16874/4, Colored Code
Wire Gauge (AWG)	#26 AWG Wire
Shell Material	Aluminum
Shell Finish	Electroless Nickel
Insulator Material	Contact size 9 to100 = liquid crystalline polymer, contact arrangements 7C2 or 24C4 = Diallyl phthalate
Hardware	HARDWARE=B .092 dia mtg holes
Coupling	Friction Coupling
Current Rating	3 A max.
Dielectric Withstanding Voltage	600 VAC at sea level 150 VAC at 70,00' altitude
Insulator Resistance	5000 megohms min.
Thermal Shock	-55°C to +200°C
Physical Shock	50 G's, 3 axes, 6 milisecond duration sawtooth pulse
Vibration	20G's, 10-2000 Hz. 12 hours
Durability	500 cycles of mating and unmating, 500 CPH max.
Moisture Resistance	Insulator resistance > 100 megohms
SaltSpray	48 hours

Specifications and dimensions subject to change.