

## Technical data sheet

Article number:  
111-00698

T30R



<b>Product Group</b>	Cable Ties for higher chemical resistance for temperatures up to +170 °C in Ethylentetrafluorineethylene
<b>Product Family</b>	T-Series in E/TFE (Tefzel®)
<b>Material</b>	Ethylene Tetrafluoroethylene (E/TFE)
<b>Colour</b>	Blue (BU)
<b>Application Range</b>	High Temperature Environments
<b>Application Tool</b>	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP
<b>Bundle Ø max.</b>	36.0 mm
<b>Bundle Ø min.</b>	3.0 mm
<b>Flammability</b>	UL 94 V0
<b>Length (L)</b>	150.0 mm
<b>Min.Tensile Strength</b>	133.3 N
<b>Operating Temperature</b>	-80 °C to +170 °C
<b>Package Content</b>	100 pcs.
<b>Package Content packed in</b>	pack
<b>Releasable Closure (Yes/No)</b>	No
<b>Specifications</b>	ANSI/UL 1565, ANSI/UL 62275
<b>Thickness (T)</b>	1.2 mm
<b>Toothing (Serration)</b>	Inside Serrated
<b>UL-File Number</b>	E64962
<b>UV-Stabilised</b>	Yes
<b>Variant</b>	Inside Serrated
<b>Weight/Unit</b>	0.001151 kg
<b>Width (W)</b>	3.5 mm

