



CONNECTOR HOUSINGS



✓ Active

TE CONNECTIVITY (TE) AMP POWER DBL LOCK PLUG HSG 3P(GWT) [Power-Signal Double Lock](#) | [Power Double Lock](#)

5-179938-1
TE Internal Number: 5-179938-1

- [Always EU RoHS/ELV Compliant](#)
- Connector System **Wire-to-Board, Wire-to-Wire**
- Centerline **6.5 mm [.256 in]**
- Number of Positions **3**
- Number of Rows **1**
- Housing Material **Nylon 6/6**



No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Connector System	Wire-to-Board, Wire-to-Wire
	Connector Style	Plug
	Sealed	No
	Applies To	Printed Circuit Board, Wire/Cable
	Product Type	Connector
	Connector Type	Housing
Configuration Features	Number of Positions	3
	Number of Rows	1

	Selectively Loaded	No
	Preloaded	No
Electrical Characteristics	Operating Voltage (VAC)	300
Body Features	Sealable	No
Contact Features	Contact Type	Socket
	Shunts/Shorting Bars	Without
	Multiple Contact Types	Without
Mechanical Attachment	Contact Retention	Without
Housing Features	Centerline	6.5 mm [.256 in]
	Housing Material	Nylon 6/6
	Housing Color	Natural
Dimensions	Height	20.6 mm [.811 in]
Usage Conditions	Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
Operation/Application	Assembly Integration Feature	Without
	For Use With	Double Lock Plate 316062-1, Header: 179846
Identification Marking	Circuit Identification Feature	Without
Industry Standards	CSA Rating	Certified
	CSA File Number	LR7189
	UL Rating	Recognized
	CSA Certified	Yes
	VDE Tested	Yes
	Agency/Standard	CSA, UL
	UL File Number	E28476
Packaging Features	Packaging Quantity	150

Product Compliance

Statement of Compliance
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

