

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-RD-A2

CATALOG LISTING

BZ-RD-A2

PAGE 1 OF 1

REPLACES

RELEASE NO.

M

ISSUE

7

CHECK

CHECK

ZUMER

DAW

CHECK

MAR 64

DAW

CHECK

MAR 64

DAW


CHECK

REVISIONS

A	CO	15200
W L K	18 MAR 64	
B	CO	2023845
M B F	22 JAN 68	
C	CO	73287-J
J A L	22 NOV 93	
D	CO	77589
J A L	30 MAR 94	
E	203155	
CSL	24 MAY 01	

3X 6-32 UNC X (.219)
BINDING HEAD COMBINATION
TERMINAL SCREW AND
CUPWASHER

NOTE -

MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000±.002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE----- 6-9 1/2 OZ

RELEASE FORCE----- 4 OZ MIN

DIFFERENTIAL TRAVEL----- .0002-.0005

OVERTRAVEL----- .060 MIN

ELECTRICAL DATA**CONTACT ARRANGEMENT**
S P D T

L103 15A 125, 250 OR 480 VAC
1/8HP 125 VAC, 1/4HP 250 VAC

L288
L299
L306



16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT .064 LB

RASTER

-50378

DRAWN

MAR 64

DAW

CHECK

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-RD-A2**BZ-RD-A2****M**DRAWING
NUMBERISSUE
3

6

REPLACES

RELEASE NO.

CHECK

REVISIONS

A	CO-15200	W L K	18 MAR 64
B	CO-023645	M B F	22 JAN 65
C	CO-73287-J	J A L	22 NOV 93
D	CO-77589	J A L	30 MAR 94

CHECK

21 MAR 64

DAW


CHECK

MAR 64

W L K

DRAWN

O-50378



NOTE -

MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE----- 6-9 1/2 OZ
RELEASE FORCE----- 4 OZ MIN
DIFFERENTIAL TRAVEL----- .0002-.0005
OVERTRAVEL----- .060 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D TUNDERWRITERS' LAB. INC. LISTED RATING
-L103- 15 A-125, 250 OR 480 VAC
1/8 HP-125 VAC; 1/4 HP-250 VAC**SCALE FULL**

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT .064 LB