


REV.	DATE	DESCRIPTION
A	02/08/03	UPDATE DRAWING FORMAT



NOITE:
1. CONTACT PIN TO SOLDER

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex										
7						DRAWN	G.R.S.						02/08/03					
6						CHECKED												
5	COVER	BRASS	GOLD	1					PART DESCRIPTION									
4	INSULATOR	DELRIN	NATURAL	1					MCX R/A SOLDER PLUG (FOR .085”, .086” SEMI RIGID CABLE)									
3	CONTACT PIN	BRASS	GOLD	1					PART NO.									
2	INSULATOR	TEFLON	NATURAL	1					252109									
1	HOUSING/BODY	BRASS	GOLD	1														
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE		C:/252/252109.DWG		DWG. NO.	252109.DWG	REV.	A	SIZE	A	SCALE	NA