



**Part Number :** [2061070003](#)

**Product Description :** USB 2.0 Female-to-Pico-Lock Female Cable Assembly, 1.0m Length, Black

**Series Number :** 205403

**Status :** Active

**Product Category :** Power and Signal Cable Assemblies



---

## Documents and Resources

### Drawings

[2061070003\\_sd.pdf](#)


### Specifications

[2012410586-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Power and Signal Cable Assemblies
Series	205403
Description	USB 2.0 Female-to-Pico-Lock Female Cable Assembly, 1.0m Length, Black
Assembly Configuration	Dual Ended Connectors
Connector to Connector	USB-to-Pico-Lock
Keyword	Pico-Lock 1.5
Product Name	Pico-Lock,USB 2.0 Hub Solutions
UPC	191128754408

### Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	30V AC

### Physical

Cable Length	1.0m
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Black
Gender	Female-Female
Net Weight	37.460/g
Number of Rows	1
Overmolded	Yes
Packaging Type	Bag
Single Ended	No

Wire/Cable Type	N/A
-----------------	-----

---

This document was generated on Jun 07, 2026