




Extended Length ("L2")	Typical Retracted Length ("L1")
60.0 Inches - 69.0 Inches	21.5 Inches
1,524.0MM-1,752.6MM	546.1MM

Scale	1:1							Name
TOLERANCE						Drawn	11.02.11	Chappel
X.X	±0.40					Approved		
X.XX	±0.25							
X.XXX	±0.15							
Angle	±3°							
								
			Modification	Date	Name			

RoHS
Complaint

Item No.	
AT-C-26-6/6/W-5-OE	
Title NON-UL 26 AWG (0.12X12)*6C, O.D.: 2.4*6.8MM, Reverse Plug, 50μ" of contact plating, WHITE	
Drawing No.	rev00
Replace	Sheet