

Product data sheet

Specifications



PB Busway Tap Off Unit, w/ Metering, 3x1 pole 3 Wire 20A, 3 Drop Cords,3f,5f,7f, L5-20, 120V

PBP4A31L520M1

⚠ Discontinued

Overview

Presentation	Factory-assembled and tested, the metered tap off units house a PowerLogic power meter, standard circuit breakers and a pre-terminated cord set. No tools required for installation on 100A, 225A, or 400A busway straight sections.
Lead time	Usually Ships within 3 Weeks

Main

Main Output Voltage	120 V
Provided Equipment	Installation guide

Physical

Color	Black
Height	14.02 in (35.6 cm)
Width	8.46 in (21.5 cm)
Depth	5.71 in (14.5 cm)
Product Weight	22.99 lb(US) (10.43 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	60 Hz
-----------------	-------

Output

Max current draw	20 A
Number of power socket outlets	3 NEMA L5-20R
Cord Length	3 ft (0.9 m) 5 ft (1.5 m) 7 ft (2.1 m)

Conformance

Product Certifications	cUL Listed CSA UL Listed
------------------------	--------------------------------

Environmental

Ambient air temperature for operation	14...104 °F (-10...40 °C)
---------------------------------------	---------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-22...158 °F (-30...70 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...15000 ft (0.0000000000...4572.0000000000 m)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------