

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/2/20	


APPROVED: _____


DATE: _____ TITLE: _____





RECOMMENDED PCB LAYOUT





SPECIFICATIONS:
Material:
Insulator: Hi-Temp Thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating:
Gold flash over Nickel underplate overall
Electrical:
Current rating: 2.0 Amp
Contact resistance: 20 mohms max.
Insulation resistance: 1,000 Mohms min.
Dielectric withstanding voltage: 500 VAC For 1 Minute
Temperature Rating:
-40°C to +105°C
Environmental:
Lead free, RoHS compliant

RoHS COMPLIANT

Positions: 06 thru 64
A = .079 [2.00] x No. of Spaces
B = .079 [2.00] x No. of Positions per row + .627 [15.92]
C = .079 [2.00] x No. of Positions per row + .248 [6.30]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	LH	12/2/20
CHECKED	JL	12/2/20
APPROVED		

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: LATCHED BOX HEADER, VERTICAL, SMT
WITH LONG LATCHES, GOLD PLATED

SIZE	PART NO.	REV.
X	2MHR-B1-XX-VUAL-SMT	-

REF: S00111C | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.