

Product data sheet

Specifications



InRow SC System 2 InRow SC units, 1 NetShelter SX Rack 600mm, and Rear Containment

RACSC201

Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

Main

Main Input Voltage	200 V 208 V 220 V 230 V 240 V
Input Connection Type	NEMA L6-20P
Number of rack unit	42U
Number of cables	1
Provided equipment	Installation guide

General

Compressor type	Rotary
Air discharge option	Horizontal
Intake air option	Rear return
Refrigerant load	1.36 kg
Air flow	566.34 l/s
Inrush current	56 A
Condensate pump flow	0.00 m3/h

Physical

Colour	Black
Height	199.1 cm
Width	120 cm
Depth	127.3 cm
Product weight	509.5 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Input power	2940 W
Network frequency	60 Hz

Environmental

Acoustic level	80 dBA
----------------	--------

Communications & Management

Control panel	Multifunction LCD status and control console
---------------	--

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Take-back	Take-back program available

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------

Recommended replacement(s)