



TOP VIEW



SIDE VIEW



Specifications

Description	Value	Unit
Shape	Round	
Resonant Frequency	400	(Hz)
Frequency Range	400 ~ 4,000	(Hz)
SPL @ 10cm	85	(dBA)
Impedance	8	(Ohm)
Cone Material	Paper	
Nominal Power	0.5	(W)
Max Power	1	(W)
Mount Type	Flush Mount	
Operating Temperature	-25 ~ +55	°C
Storage Temperature	-25 ~ +55	°C
Weight	42	(g)

Notes

- 1) All dimensions are in mm unless otherwise noted
- 2) All parts meet RoHS



DB UNLIMITED

Revision History

Version	Description			Date	Approved
1	Released from Engineering			2/5/2014	J.S.

Dynamic Speaker

SP570408-2