Part Number : 732760112
Product Description : N Plug, Straight, Crimp, LMR-400 Cable, Brass Body, Nickel (Ni) Plated, One Piece Per Bag, 50 Ohms
Series Number : 73276
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

732760112_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73276
Description	N Plug, Straight, Crimp, LMR-400 Cable, Brass Body, Nickel (Ni) Plated, One Piece Per Bag, 50 Ohms
Application	RF
Product Name	N
Style	Cable
Type	Medium
UPC	884982654945

Electrical

Frequency	11 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 1000 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	43.000/g
Orientation	Straight
Packaging Type	Individual Bag
Panel Mount	No

Downloaded from Arrow.com.

Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	LMR-400

Downloaded from Arrow.com.