


ACTUATOR COLOR:  
IVORY



- NOTES:
1. ALL DIMENSIONS IN MM
  2. GENERAL TOLERANCE: X: X=±0.4  
X:XX=±0.25
  3. TERM. NOS. FOR REFERENCE ONLY.
  4. RATING: 12VDC, 50mA
  5. OPERATING FORCE 260 ± 50 gf
  6. TRAVEL: 0.25mm +0.2/-0.1mm
  7. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
  8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES.
  9. CONTACT MATERIAL: SILVER
  - ▲ 10. 2002/95/EC (ROHS) COMPLIANT
  11. PACKAGING: TAPE AND REEL; 750 PIECES PER REEL
  12. ▲ DENOTES CRITICAL PARAMETER

**E-SWITCH®**

TITLE TL3301SPF260QG

C	21068	ADD OPERATING FORCE	3/15/13	EBP
B	20775	UPDATED, CONVERTED INVENTOR	9/25/12	RC
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	4:1	DATE	9/25/2012	DR	RC	DWG	P010799	REV	C
-------	-----	------	-----------	----	----	-----	---------	-----	---