

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-2RQ241-D5

ALK7675

BZ-2RQ241-D5
PAGE 1 OF 1

M

DRAWING
NUMBER

6

ISSUE

REPLACES X92114-BZ

RELEASE NO. PR-18144-T

12SEP07

PSR

CHECK

17 FEB 06

17 FEB 06

17 FEB 06

17 FEB 06


17 FEB 06

17 FEB 06

17 FEB 06

17 FEB 06

17 FEB 06



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 SWITCH WILL WITHSTAND TEMPERATURES OF 250°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE — — — — — 9-13 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE — — — — — 4 OZ MIN	L96 15A 125, 250 OR 480 VAC 1/8 HP 125 VAC, 1/4 HP 250 VAC 1/2A 125 VDC, 1/4A 250 VDC	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES TOLERANCES ARE
DIFFERENTIAL TRAVEL — — — .0004-.0020	L288 L306 L310 L315	ONE PLACE (.01) ± .030 TWO PLACE (.001) ± .015 THREE PLACE (.000) ± .008
OVERTRAVEL — — — — — .219 MIN	CE     16A 250V ~ T85 5E4	ANGLES ± WEIGHT .086 LB

RASTER

FO-52848

DRAWN

17 FEB 06

17 FEB 06