
Part Number : 1300660115
Product Description : BradPower D-Size (1 3/8”–M35) Receptacle, 3 Poles, Female, 1/2" - 14 NPT, 10 AWG, 5.0m (16.40') Length
Series Number : 130066
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : CR3000A30M050



Documents and Resources

Drawings

1300660115_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Connectors
Series	130066
Description	BradPower D-Size (1 3/8”–M35) Receptacle, 3 Poles, Female, 1/2" - 14 NPT, 10 AWG, 5.0m (16.40') Length
IP Rating	IP67
Product Name	BradPower D-Size
Type	Single Ended (pigtail)
UPC	78678887232

Agency

UL	E258922

Electrical

Current - Maximum per Contact	32.0A
Voltage - Maximum	600V AC/DC

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	5.0m
Material - Component	Clear Annodized Aluminum
Mounting Thread Size	1/2" - 14 NPT
Net Weight	1021.000/g
Orientation	Straight
Panel Mount	Front

Downloaded from Arrow.com.

Poles	3
Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	UL 1015
Wire Size (AWG)	10

Downloaded from Arrow.com.