Part Number : 366480028
Product Description : 2.13mm Diameter MLX Pin and Socket Receptacle, 15 Circuit, Black
Series Number : 36648
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

366480028_sd.pdf

PK-42022-XX-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-42022-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	36648
Description	2.13mm Diameter MLX Pin and Socket Receptacle, 15 Circuit, Black
Application	Wire-to-Wire
Comments	Maximum current per contact 20A if used with 36663 and 36664 terminal
Component Type	Receptacle
Product Name	MLX
UPC	884982487604

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	15
Color - Resin	Black
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Nylon

Downloaded from Arrow.com.

Number of Rows	3
Packaging Type	Carton
Panel Mount	Yes
Pitch - Mating Interface	6.35mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-55° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.13mm Diameter MLX Power Crimp Housing Plugs	42021

Use with Part(s)

Description	Part Number
MLX Male Crimp Terminals	42023
MLX Female Crimp Terminals	42024

Downloaded from Arrow.com.