

Representative Image

Catalog No. TC376

Description: STAND-OFF BRKT MTG BASE 1.75IN NAT

UPC No 5414363058793

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Stand-Off Brackets Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 44.45mm (1.75 Inches), Width of 17.5mm (0.69 Inches), Height of 17.0mm (0.67 Inches), Screw Mounting Method, Mounting Hole Diameter of 4.8mm (0.189 Inches)

Descriptors

Category	Cable tie mounts
Special Features	These brackets permit bundles to be mounted on either side. They also serve as means to raise bundles off the surface.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	44.45 mm
Length	1.75 inch
Width	17.5 mm
Width	0.69 inch
Height	17 mm
Height	0.67 inch
Type of fastening	Other
Diameter mounting hole	4.8 mm
Material	Plastic

by ABB

Downloaded from Arrow.com.

ETIM	EC000449 Mounting base and -element for cable ties
Material quality	Polyamide (PA)
Colour	Natural colour

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	ZODZ	N/A	N/A

Downloaded from Arrow.com.