
C2G

C2G
Discontinued - 19.7ft (6m) SC-SC 9/125 OS2 Duplex Single-Mode Fiber Optic Cable - Yellow

Part No. 11217



Cost-effective solution that provides high bandwidth and transmission rates over longer distances. This high quality fiber optic patch cable is specifically designed for gigabit ethernet applications. The patented injection molding process provides each connection greater durability in resisting pulls, strains and impacts from cabling installs.

Each cable is 100% optically inspected and tested for insertion loss before you receive it. A pull-proof jacket design surrounds the popular 9/125 Single-mode fiber, immune to electrical interference.

Features & Benefits

- Designed to support gigabit ethernet applications
- Patented injection molding process for greater durability
- Optically inspected and tested for insertion loss
- Pull-proof jacket design, immune to electrical interference

Specifications

General Info

Product Line	C2G	Color	Yellow
UPC Number	757120112174	Country Of Origin	Hong Kong
Application Sector	Commercial, Industrial	Warranty Type	Lifetime
Type	Cable		

Dimensions

Product Length US	19.7 FT	Cable Length	19.7 ft

Technical Information

Fiber Optic Cable Type	OS2, Single-Mode	Jacket Material	PVC (Polyvinyl Chloride)
Bend Radius	45 mm	Simplex/Duplex	Duplex
Cable Type	Fiber Optic	Jacket Rating	Standard / Non-Rated
Connector 2	SC Male	Connector 1	SC Male
Fiber Size	9/125		

Downloaded from Arrow.com.