


REV.	DATE	DESCRIPTION
A	12/09/04	MODIFY OVERALL PART LENGTH



PCB MOUNTING HOLES

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex								
8						DRAWN	G.R.S.					12/09/04				
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	CHECKED		PART DESCRIPTION MCX P.C. BOARD RECEPTACLE JACK - 75ohm (3.94 [.155"] LEGS)								
6						ISSUED										
5					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	SHEET	1 OF 1	PART NO. 252105-75								
4																
3	CONTACT PIN	BER. COPPER	GOLD	1		DWG FILE C:/225/252105-75.DWG		DWG. NO.		252105-75.DWG	REV.	A	SIZE	A	SCALE	NA
2	INSULATOR	TEFLON	NATURAL	1												
1	BODY	BRASS	GOLD	1												
DESCRIPTION					MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING								