

YAV10T3BOX, Uninsulated Ring Terminal, #14-10 AWG Str, #12-10 Sol, 1-Hole, 1/4" Stud

By Burndy
Catalog # [YAV10T3BOX](#)



Uninsulated Ring Terminal For 12 - 10 AWG

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors, Industrials, Hospitals, Electric Utilities, Shipboard And Marine, Computers, Steel Mills, Mining Equipment And Other Equipment That Is Subject To Vibration Or Requiring Dependable Electrical Performance

Specifications

Buy American Compliant	Yes
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	<ul style="list-style-type: none"> • Buy America Compliant (All status valid till December 2025) • Buy American Act Compliant (All status valid till December 2025) • BABA Compliant (All status valid till December 2025)
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM

Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	<ul style="list-style-type: none"> • 14 AWG • 12 AWG • 10 AWG
Conductor - Copper Solid Size	<ul style="list-style-type: none"> • 12 AWG • 11 AWG • 10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	14 AWG-10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.21 in
Dimension - L Length Overall mm	28 mm
Dimension - Pad Width inch	0.47 in
Package Height	0.000 in
Dimension - Strip Length inch	7/16 in
Dimension - Stud Size inch	1/4 in
Dimension - B Length fraction	16/41 in
Dimension - B Length inch	0.39 in
Dimension - Z inch	0.32 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Size fraction	1/4
Dimension - Length Overall inch	1.1 in
Dimension - D inch	0.57 in
Dimension - N inch	0.23 in

General

Trade Name HYLUG™
Sub Brand HYLUG
Physical Attribute - Tongue Ring
Type
Plated Y
Feature - Barrel Type Standard
Feature - Barrel Style Chamfered
Type Ring Tongue
UPC 14 Digit GTIN 00781810541708
Material Copper

Plating Type Tin - Electro Plated
UPC 781810541708

Logistics

Minimum Pack Quantity 50
Carton Quantity 600
Pallet Quantity 99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YAV10T3BOX-SPEC-EN | REV 4/2026