
CUC-V06-F1PGY-UBA/UBBB - Panel mounting frame set

1411904

https://www.phoenixcontact.com/us/products/1411904

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



USB socket insert, 4-pos., USB socket type A to USB socket type B, socket type A to panel mounting frame side, for the Freenet system in the panel mounting frame, IP20 terminal outlet, 19" patch panel, and service interface

Your advantages

- IP67 protection class
- Easy assembly

Commercial data

Item number	1411904
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AB14
Product key	ABNNFC
GTIN	4046356945011
Weight per piece (including packing)	17.98 g
Weight per piece (excluding packing)	14.335 g
Customs tariff number	85366990
Country of origin	DE

Downloaded from Arrow.com.

Technical data

Product properties

Product type	Panel-mount frame
Type	USB-A
Number of positions	4
Connection profile	USB

Electrical properties

Rated voltage (III/3)	30 V
Rated current	1 A
Transmission medium	Copper
Transmission speed	480 Mbps
Transmission characteristics (category)	USB 2.0

Material specifications

Color	gray
Material	Plastic
Flammability rating according to UL 94	V0
Housing material	Plastic
Cable seal material	NBR
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	PC
O-ring material	FPM

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 1000

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-15 °C ... 65 °C

Downloaded from Arrow.com.

Classifications

ECLASS

ECLASS-15.0	27440390
ECLASS-13.0	27440390

ETIM

ETIM 9.0	EC004746

UNSPSC

UNSPSC 21.0	39121400

Downloaded from Arrow.com.

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com

Downloaded from Arrow.com.