881607-1 Product Details



Active

View 3D PDF

FASTON Uninsulated Receptacles & Housings

.110S FASTON REC.

881607-1

TE Internal Number: 881607-1

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Product Highlights View All

- Terminal
- Terminal Type = Receptacle
- Mating Area Interface Dimensions = 2.79 x 0.8 mm
- Board Mount = No
- Receptacle Style = Straight

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Product Type	Terminal
Receptacle Style	Straight
Insulation Support	Insulation Support
Wire/Cable Type	Stranded
Insertion Force	Low
Finish	None

Mechanical Attachment

Board Mount	No

Termination Features

Crimp Type	F-Crimp

Dimensions

Mating Area Interface Dimensions (mm [in])	2.79 x 0.8 [.110 x .032]
Insulation Diameter (mm [in])	2.00-2.70 [.079-.106]
Length (mm [in])	14.50 [0.571]

Body Features

Wire Range (mm [AWG])	0.50-1.00² [20-17]
Material	Brass
With Dimple	With
Stock Thickness (mm [in])	0.25 [0.010]

Contact Features

Terminal Type	Receptacle

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

For Hermetic Header Tab	No
Temperature Range (°C)	90

Packaging Features

Packaging Quantity	1

Other

Line	FASTON .110
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

[+] Provide Website Feedback

Downloaded from Arrow.com.