Part Number : 640017400
Product Description : PremiumGrade Hand Crimp Tool for Industrial Terminals, 22-10 AWG (see ATS)
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents and Resources

Tooling Specifications

ATS-640017400-001.pdf
TM-640160065-001.pdf
TM-640160065CN-001.pdf
TM-640160065DE-001.pdf
TM-640160065SP-001.pdf
TM-640160065FR-001.pdf
TM-640160065IT-001.pdf
TM-640160065JP-001.pdf
TM-640160065KR-001.pdf
TM-640160065MY-001.pdf
TM-640160065PL-001.pdf
TM-640160065RU-001.pdf
TM-640160065SK-001.pdf
TM-640160065TH-001.pdf
TM-640160065VN-001.pdf
TM-640160065TW-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant

Downloaded from Arrow.com.

Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	PremiumGrade Hand Crimp Tool for Industrial Terminals, 22-10 AWG (see ATS)
Comments	ServiceGrade Hand Tool 640160041; Type: 4C
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	800756778624

Downloaded from Arrow.com.

Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	742.798/g

Applicable Parts

Description	Part Number
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5), Carton	191640003
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 1/4" (M6), Carton	191640004
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 3/8" (M9), Carton	191640005
Perma-Seal Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Carton	191640006
Perma-Seal Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 8 (M4), Carton	191640007

Downloaded from Arrow.com.

Perma-Seal Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5), Carton	191640008
Perma-Seal 3-Way Connector Assembly for 22-18 AWG Wire, Carton	191640011
Perma-Seal Butt Splice for 22-18 AWG Wire, Carton	191640013
Perma-Seal Butt Splice for 22-18 AWG Wire, Mylar Tape Carrier	191640014
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 3/8" (M9), Carton	191640020
Perma-Seal Hook Tongue Terminal for 16-14 AWG Wire, Stud Size 10 (M5), Carton	191640021
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 1/4" (M6), Carton	191640026
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 5/16" (M8), Carton	191640027
Perma-Seal Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5), Carton	191640028
Perma-Seal Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton	191640029
Perma-Seal Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 10 (M5), Carton	191640030
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5), Carton	191640032
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton	191640033
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 10 (M5), Carton	191640034
Perma-Seal 3-Way Connector	191640042

Downloaded from Arrow.com.

Assembly for 16-14 AWG Wire, Carton	
Perma-Seal Step Down Butt Splice from 16/14 to 22/18 AWG Wire, Carton	191640043
Perma-Seal Butt Splice for 16-14 AWG Wire, Carton	191640044
Perma-Seal Butt Splice for 16-14 AWG Wire, Mylar Tape Carrier	191640045
Perma-Seal Butt Splice for 12-10 AWG Wire, Carton	191640056
Perma-Seal Butt Splice for 12-10 AWG Wire, Mylar Tape Carrier	191640057
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/2" (M12), Carton	191640058
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 6 (M3.5), Carton	191640061
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Carton	191640062
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Carton	191640065
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Carton	191640066
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 5/16" (M8), Carton	191640067
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 3/8" (M9), Carton	191640068
Perma-Seal Spade Tongue Terminal for 12-10 AWG Wire, Stud Size 6 (M3.5), Carton	191640069
Perma-Seal Spade Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Carton	191640070
Perma-Seal 3-Way Connector	191640074

Downloaded from Arrow.com.

Assembly for 12-10 AWG Wire, Carton	
Perma-Seal Step Down Butt Splice from 12/10 to 16/14 AWG Wire, Carton	191640077
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Carton	191640085
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 8 (M4), Carton	191640086
Perma-Seal Hook Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5), Carton	191640141
Perma-Seal Hook Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton	191640142
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	191640306
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 3/8" (M9), Mylar Tape Carrier	191640307
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier	191640308
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 5/16" (M8), Mylar Tape Carrier	191640309
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier	191640310
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier	191640311
Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	191640312
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	191640316

Downloaded from Arrow.com.

Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier	191640317
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 5/16" (M8), Mylar Tape Carrier	191640318
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier	191640419
Perma-Seal Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 5/16" (M8), Carton	191640435
Perma-Seal Step Down Butt Splice from 12/10 to 16/14 AWG Wire, Mylar Tape Carrier	191640582
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 3/8" (M9), Mylar Tape Carrier	191640857
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier	191640938
Perma-Seal Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	191640939
Perma-Seal Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5),Mylar Tape Carrier	191640948

Downloaded from Arrow.com.