Part Number : 1727040184
Product Description : FCT Metal Backshell for D-Sub Connector, Shell Size 3, Straight Cable Outlet, with Rubber Bushing and #4-40 Knurled Thumb Screws
Series Number : 172704
Status : Active
Product Category : D-Sub Backshells
Engineering Number : FMH3R



Documents & Resources

Drawings
1727040184_sd.pdf

3D Models and Design Files
1727040184_stp.zip

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	D-Sub Backshells
Series	172704
Description	FCT Metal Backshell for D-Sub Connector, Shell Size 3, Straight Cable Outlet, with Rubber Bushing and #4-40 Knurled Thumb Screws
Magnetic	Yes
Product Name	FCT Products
Type	Rugged Metal
UPC	889056062602

Electrical

Shield Type	Solid Metal
Shielded	Yes

Physical

Cable Diameter	9.00-11.00mm
Material - Backshell	Zinc Die-cast
Material - Bushing	TPE
Material - Screw	Brass
Mounting Style	Knurled Thumb Screw Lock
Net Weight	77.200/g
Orientation	Straight
Packaging Type	Carton
Plating - Backshell	Nickel
Temperature Range - Operating	-35° to +100°C
Thread Size	4-40 UNC

Downloaded from Arrow.com.

Thread Type	Standard
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	No

Use with Part(s)

Description	Part Number
Use With	FCT D-Sub, Size 3

This document was generated on Apr 26, 2025

Downloaded from Arrow.com.