



Part Number : 150612305

Product Description : 1.00mm Pitch Premo-Flex Round Flat Cable (RFC) Jumpers, Round-to-Flat (Type B), 76.00mm Cable Length, Tin (Sn) Plating, 5 Circuits



Series Number : 15061

Status : Active

Product Category : Flat-Flexible Cable (FFC)

Documents & Resources

Drawings

[150612305_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	15061
Description	1.00mm Pitch Premo-Flex Round Flat Cable (RFC) Jumpers, Round-to-Flat (Type B), 76.00mm Cable Length, Tin (Sn) Plating, 5 Circuits
Comments	Round-to-Flat, Type B
Product Name	Premo-Flex RFC Jumper
UPC	196823685040

Electrical

Current - Maximum per Contact	1.25A
Voltage - Maximum	60V AC

Physical

Cable Length	76.00mm
Circuits (Loaded)	5
Contact Layout Type	B (round-to-flat)
Design Feature	Direct to Board
Material - Plating Mating	Tin
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-40° to +105°C
Termination Style	Solder
Wire/Cable Type	Round Flex Cable
Wire Size (AWG)	28