




Contact assignment/
Kontaktbelegung:

1	yellow / gelb	AWG22	TX +
2	white / weiß	AWG22	RX+
3	blue / blau	AWG22	RX -
4	orange / orange	AWG22	TX -
shielding / Schirmung			
5	red / rot	0,75mm ²	
6	blue / blau	0,75mm ²	

tolerance of cable/ wire <i>Kabel- / Litzentoleranz:</i>				dim. in mm		Receptacle B12, with square, Coding 1 <i>Flansch B12, Vierkant, Codierung 1</i>					
L <= 4m: L + 40mm L > 4m: L + 1%											
general tolerance/ <i>Allgemeintoleranz:</i>		drawn/ <i>gez.</i>		Date/Datum Name							
0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm ≤ ± 1,5°		09.11.2016 09.11.2016		Böckeler Schramm							
Index: a Original		scale/Maßstab: 1,5:1 (1:1 ; 2:1)				dwg no / Z.-nr.:		56K1A1058		DIN- A3	
Status: InBearbeitung											
RoHS & REACH compliant/ <i>konform</i>										1 / 1	