

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130103-0066](#)
Status: **Active**
Description: Watertite® Wet Location Incandescent Hand Lamp, 100W with TEFLON® Globe, Cord Type 16/2 SOOW, 15.24m (50.0') Cord Length

Documents:
[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA	LR85374
UL	E59049

General

Product Family	Portable Lighting
Series	130103
NEMA Configuration	NEMA 1-15
NEMA Rating	NEMA 4X
Outlet	None
Product Literature Order No	987650-8053
Product Name	Watertite®
Type	Hand Lamps
UPC	78678861335
Woodhead	Yes

Physical

Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	127.00mm (5.000")
Duty	Wet Location
Guard Included	No
Guard Type	N/A
Height	254.00mm (10.000")
Length	N/A
Material - Globe	PTFE
Material - Guard	N/A
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Incandescent
Cord Type - Primary	16/2 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC

Material Info

Old Part Number	1225
-----------------	------



image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130103Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION