



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

|            |                                                 |
|------------|-------------------------------------------------|
| Version    | Wire-end ferrule, Standard, 15 mm, 12 mm, white |
| Order No.  | <a href="#">9021170000</a>                      |
| Type       | H16,0/22T W                                     |
| GTIN (EAN) | 4008190151478                                   |
| Qty.       | 100 items                                       |
| Packaging  | loose                                           |

## Technical data

### Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

|                       |                            |
|-----------------------|----------------------------|
| UL File Number Search | <a href="#">UL Website</a> |
|-----------------------|----------------------------|

|                         |         |
|-------------------------|---------|
| Certificate no. (cULus) | E499744 |
|-------------------------|---------|

### Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 0.62 g |
|------------|--------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
|------------------------|-----------------------------|

|            |                       |
|------------|-----------------------|
| REACH SVHC | No SVHC above 0.1 wt% |
|------------|-----------------------|

### Technical data

| Description of article | Wire end ferrule with plastic collar, white | Version | Standard |
|------------------------|---------------------------------------------|---------|----------|
|------------------------|---------------------------------------------|---------|----------|

### Wire-end ferrules

|                               |                    |                                         |               |
|-------------------------------|--------------------|-----------------------------------------|---------------|
| Contact surface diameter (D1) | 5.8 mm             | Contact surface length (L2)             | 12 mm         |
| Collar diameter (D2)          | 8.8 mm             | Plastic collar thickness (S2)           | 0.4 mm        |
| L1 in mm                      | 22.00 mm           | Wire connection cross section AWG, max. | AWG 6         |
| Metal sleeve thickness (S1)   | 0.2 mm             | Stripping length                        | 15 mm         |
| Conductor cross-section       | 16 mm <sup>2</sup> | Colour code                             | Telemecanique |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000005    | ETIM 7.0    | EC000005    |
| ETIM 8.0    | EC000005    | ETIM 9.0    | EC000005    |
| ETIM 10.0   | EC000005    | ECLASS 9.0  | 27-40-02-01 |
| ECLASS 9.1  | 27-40-02-01 | ECLASS 10.0 | 27-40-02-01 |
| ECLASS 11.0 | 27-40-02-01 | ECLASS 12.0 | 27-40-02-01 |
| ECLASS 13.0 | 27-40-02-01 | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 |             |             |

Drawing

